Stationary 633 4-Way Fogger

MODEL # 950649

OVERVIEW

The Stationary 633 4-Way Fogger is a damp mist sprayer that uses compressed air (15 CFM @ 80 PSI) and venturi action to draw ready-to-use chemical solution from a nearby container and project it up to 15 feet in 4 directions. The adjustable output sprays mist (fog) into the air to cover exposed surfaces and penetrate hard-to-reach areas. This versatile unit can be used as a 2-Way fogger by closing ball valves on two fogger bodies. It can be permanently mounted or easily moved.

Key Features

- Can be permanently mounted or moved for use in multiple locations
- Atomizes and sprays chemical solutions using only compressed air
- Venturi action draws pre-diluted chemical from a nearby container
- Projects up to 15' in 4 directions
- Ball valves on two fogger bodies allow for conversion to 2-Way fogging for narrow areas
- Damp fog (mist) fills the air and covers exposed surfaces with chemical, including hard-to-reach areas
- Optional metering tips can reduce chemical usage and output wetness
- Chemical resistant polypropylene construction ensures durability and years of outstanding performance
- See Catalog 7 for hand held, permanently mounted and portable foggers
- Use the Lafferty Fogger Planning Tool to design the optimal fogging system for any facility

Includes

- Polypropylene base/mounting plate
- Table standoffs
- 1/2" NPT air inlet
- (4) Machined polypropylene fogger bodies
- (2) Air ball valves
- (4) Metering tip holders
- (2) 10' chemical suction tubes and strainers

OPTIONS

Optional Check Valves to Keep Tubes Primed Check Valve, Chemical, PP(W), 1/4" (EPDM)

For Lighter Fog Use Metering Tips (4 Sets) Metering Tips-Color Coded (10 Smallest)

Proportioning / Filling Options

1-Way Ball Valve Mixing Station (4 GPM) 1-Way Push Lever Mixing Station (4 GPM)

Quick-Disconnect Set for Air Inlet QD, SS, Plug, 1/2" MPT QD, SS, Socket, 1/2" FPT

APPLICATIONS

- Sanitizers
- Agriculture/Horticulture
- Animal Health
- Dairy
- Food & Beverage
- Industrial
- Odor Control
- Pharm/Bio
- And Many Other Applications!



REQUIREMENTS

Ready-to-Use Chemical Solution	
Compressed Air	up to 15 CFM @ 80 PSI
Minimum Air Supply Line	1/2"



443794

985100

981100

350459

350455



